


HOW TO ASSEMBLE YOUR 5—DRAWER

NO	MODEL	DESCRIPTION	QTY	NO	MODEL	DESCRIPTION	QTY
1	BE WINDING	CONFIRMAT SCREWS	20	6	ar .	CAMS	10
2	American Company of the Company of t	DOWELS	20	7	611	CAM PINS	10
3	o	BACKING NAILS	100	8	(2)	30mm 8 GAUGE INFILL SCREW	3
4	4 = 17777	5/8 X 6 WOOD SCREWS	30	9	A THE PERSON	EURO SCREWS	20
5	·	HANDLES	5	10	(<u> </u>	- INFILL	1

STEP1.

LAYOUT YOUR DRAWER PIECES FLAT AS PER DESIGN WITH PRE-DRILLED HOLES FACING UP. START WITH THE BACK OF THE FRONT DRAWER AND PLACE YOUR DOWELS & CAM PIN IN THE



STEP 2.

GRAB YOUR FIRST SIDE AND INSERT YOUR CAMS
INTO THE HOLE PROVIDED ON THE OUTSIDE OF THE
DRAWER GENTLY AS PER INSTRUCTIONS BELOW.


PRE-DRILLED HOLES ON EITHER SIDE AS INSTRUCTED BELOW.

IMPORTANT NOTICE:

PLACE THE FITTING OVER THE HOLE KEEPING THE SQUARE EDGE OF THE FITTING PARALLEL TO THE FACE OF THE BOARD, KNOCK IN CAREFULLY.

PUSH THE SIDE INTO THE FRONT DOWELS & PIN THEN CAREFULLY USING A SCREW DRIVER TURN UNTIL IT LOCKS IN. REPEAT THIS PROCESS WITH THE OTHER SIDE.

NOW PLACE YOUR LAST PIECE BETWEEN THE TWO SIDES USING THE SCREWS NO.1 SUPPLIED SCREW INTO THE SIDES OF THE BACK DRAWER PIECE.






DRAWER ASSEMBLY


STEP 3.

YOUR DRAWER SHOULD BE FACING DOWN WITH THE FRONT DRAWER EXSPOSING THE CUTOUT FOR THE BASE TO BE PUSHED INTO FACE DOWN WITH THE BROWN SIDE SHOWING. MAKING SURE YOU HAVE THE DRAWER SQUARE, PROCEED TO NAIL DOWN THE BASE SPACING THEM OUT AROUND THE EDGE OF THE THREE SIDES.



STEP 4

RUNNER PLACEMENT



PLACE YOUR RUNNERS INTO THE DESIGNATED HOLES MAKING SURE THE WHEEL IS FACING TO THE FRONT OF THE GABLE. HOLE POSITION NO 1,8 AND 15.

YOUR DRAWER RUNNER WILL HAVE THE WHEEL TO THE BACK OF THE DRAWER.


STEP 5.

USING THE HANDLE SCREW (NO:6) ATTACH THE HANDLE TO THE BACK OF THE DRAWER. FRONT INTO THE PREDRILLED HOLES ALL READY PROVIDED.



STEP 6.

PLACE YOUR DRAWER RUNNER ON THE BOTTOM OF THE DRAWER USING THE WOOD SCREWS PROVIDED (No:4) SCREW TWO INTO EACH RUNNER. REPEAT FOR THE OTHER SIDE.



PICTURE OF YOUR FINISHED





9 Nevilles Street, Underwood Qld 4119

Ph. (07) 3208 6799 Fax: (07) 3290 6332 Int Ph: +617 3208 6799 Int Fax: +617 3290 6332


INSTRUCTIONS FOR RUNNER PLACEMENT

	DIACDANAA	
30.	DIAGRAM 1	
29.	•	
	•	
28.	•	
27.	•	
26. ●	•	
25. ●	•	
24. ●	•	
23. ●	•	
22. ●	•	
21. •	•	
20. ●	•	
19. • ←	5mm HOLES •	
18. ●	•	
17. ●	•	
15. ●	•	
15. •	•	
14. •	•	
13. ●	•	
12 . ●	•	
11. •	•	
10.	•	
9. •	•	
©°• °	00 00 0 00	
8. •	•	
7.	•	
6. ●	•	
5. ●	•	
4. ●	•	
3. ●	•	
2.	•	
1. •	•	
*	* *	
•		

* = FIXED SHELF HOLES & KICK

Place metal runners in their correct hole positions (see above DIAGRAM 1) making sure CL = LEFT HAND GABLE & CR = RIGHT HAND GABLE, then attach using the special 7.5 euro screws provided. (see diagram to the right).

	<u>ties</u>						
Models	Hole Positions	Fixed S	Shelf Position				
EXC – 4J	1 – 8 – 15 - 22	N/A					
EXC – 5C	1 – 8 – 15 – 20 – 25 N/A		\				
EXC – 4B	8 – 16 – 24 - 32	N/A	1				
EXC – 2B	8 – 14	N/A	N/A				
EXB - 5C	1 – 8 – 15 – 20 – 2	25 N/A	N/A				
EXB – 4J	1 – 8 – 15 – 20	N/A	N/A				
EXB – 4B	8 – 16 – 22 – 28	N/A	N/A				
	Executive 750 'H' SERIES						
Models	Hole Positions	CAM PIN	CAM PIN-Hole Positions				
HS		8					
H1	1	8					
H2	1 – 6	11					
H3	1 – 8 – 13	1 – 8 – 13 20					
	MAXI U	MAXI ULTRA 'H' SERIES					
Models	Hole Positions CAM PIN-Hole Positions						
H1	1	8					
HS2	1	8 –	8 – 15				
H2	1 – 8	13	13				
HS	8						
	MAXI ULTRA & ULTRA SERIES						
	MAXI ULTRA &	ULTRA S	SERIES				
Models	MAXI ULTRA & Hole Positions	ULTRA S Models	SERIES Hole Positions				
Models 450							
	Hole Positions	Models	Hole Positions				
450	Hole Positions 1-6-11-16	Models LSD550	Hole Positions				
450 315C	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21	Models LSD550	Hole Positions 1-8 1				
450 315C	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21	Models LSD550 LSD330	Hole Positions 1-8 1				
450 315C 515	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21 MAXI	Models LSD550 LSD330	Hole Positions 1-8 1 SRIES Shelf Position				
450 315C 515 Models	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21 MAXI Hole Positions	Models LSD550 LSD330 & MSM SE Fixed	Hole Positions 1-8 1 SRIES Shelf Position				
450 315C 515 Models 16J3	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21 MAXI Hole Positions 1 - 8 - 15	Models LSD550 LSD330 & MSM SE Fixed 22 25 36	Hole Positions 1-8 1 SRIES Shelf Position 2				
450 315C 515 Models 16J3 C16	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21 MAXI Hole Positions 1 - 8 - 15 1 - 8 - 15 - 20 - 20	Models LSD550 LSD330 & MSM SE Fixed 22 25 36	Hole Positions 1-8 1 SRIES Shelf Position 2				





WARRANTY

Our goods come with guarantees that cannot be excluded under the Australian Consumer Law. You are entitled to a replacement of refund for major failure.

10 Year Warranty

- If the purchaser has a fault or defect with this product, the purchaser needs to contact Multistore Industries (Aust) directly on (07) 3208 6799 and state date of purchase, place of purchase and proof of purchase.
- Multistore Industries (Aust) will replace any faulty or defect parts at no cost to the customer. A replacement will be sent to you as soon as possible, or product can be exchanged at the store of purchase.
- This warranty is in addition to other rights and remedies of the customer under law.
 Sincerely,

Multistore Industries (Aust) Management