

3 x DRAWER ASSEMBLY INSTRUCTION


NO	MODEL	DESCRIPTION	QTY
1	BE MINIMUM.	CONFIRMAT SCREWS	12
2		DOWELS	12
3	o——	BACKING NAILS	60
4	4	5/8 X 6 WOOD SCREWS	18
5	•── NFL UUS 965	INFILL	1


NC)	MODEL	DESCRIPTION	QTY
6		38	CAMS	6
7		GIVE	CAM PINS	6
8		& Decommon.	30mm 8 GAUGE SCREW	3
9		A THE STATE OF	EURO SCREWS	12
10			HANDLE	3
11			RUNNERS PER SET	3

STEP 1.

LAYOUT YOUR DRAWER PIECES FLAT AS PER DESIGN WITH PRE-DRILLED HOLES FACING UP.

START WITH THE BACK OF THE FRONT DRAWER AND PLACE YOUR DOWELS & CAM PIN IN THE PRE-DRILLED HOLES ON EITHER SIDE AS INSTRUCTED BELOW.






STEP 2.

GRAB YOUR FIRST SIDE AND INSERT YOUR CAMS INTO THE HOLE PROVIDED ON THE OUTSIDE OF THE DRAWER SIDE GENTLY AS PER INSTRUCTIONS BELOW.



IMPORTANT NOTICE:

PLACE THE FITTING OVER THE HOLE KEEPING THE SQUARE EDGE OF THE FITTING PARALLEL TO THE FACE OF THE BOARD, KNOCK IN **CAREFULLY**.



PUSH THE SIDE INTO THE FRONT DOWELS & PIN AND THEN CAREFULLY USING A SCREW DRIVER TURN UNTIL IT LOCKS IN. REPEAT THIS PROCESS WITH THE OTHER SIDE.


NOW PLACE YOUR LAST PIECE BETWEEN THE TWO SIDES USING THE SCREWS SUPPLIED SCREW INTO THE SIDES OF THE BACK DRAWER PIECE.



DRAWER ASSEMBLY


STEP 3.

YOUR DRAWER SHOULD BE FACING DOWN WITH THE FRONT DRAWER EXSPOSING THE CUTOUT FOR THE BASE TO BE PUSHED INTO FACE DOWN WITH THE BROWN SIDE SHOWING. MAKING SURE YOU HAVE THE DRAWER SQUARE, PROCEED TO NAIL DOWN THE BASE SPACING THEM OUT AROUND THE EDGE OF THE THREE SIDES.



STEP 4.

RUNNER PLACEMENT




PLACE YOUR RUNNERS INTO THE DESIGNATED HOLES MAKING SURE THE WHEEL IS FACING TO THE FRONT OF THE GABLE. HOLE POSITION NO 1, 8 AND 15.

YOUR DRAWER RUNNER WILL HAVE THE WHEEL TO THE BACK OF THE DRAWER.

STEP 5.


USING THE HANDLE SCREW (NO:5) ATTACH THE HANDLE TO THE BACK OF THE DRAWER FRONT INTO THE PREDRILLED HOLES ALREADY PROVIDED.





STEP 6.

PLACE YOUR DRAWER RUNNER ON THE BOTTOM OF THE DRAWER USING THE WOOD SCREWS PROVIDED (No:4) SCREW TWO INTO EACH RUNNER. REPEAT FOR THE OTHER SIDE.



PICTURE OF YOUR FINISHED DRAWER



Multistore Industries (Aust) Pty Ltd

9 Nevilles Street, Underwood, QLD 4119

Tel-(07) 3208 6799

Fax- (07) 3209 6332

www.multistore.com.au

sales@multistore.com.au



9 Nevilles Street, Underwood Qld 4119

Ph. (07) 3208 6799 Fax: (07) 3290 6332 Int Ph: +617 3208 6799 Int Fax: +617 3290 6332


INSTRUCTIONS FOR RUNNER PLACEMENT

	DIAGRAM 1	
30.		•
29. •		•
28. •		•
27. •		•
26. •		•
25. •		•
24. •		•
23. •		•
22. •		•
21. •		•
20. •		•
19.	5mm HOLES	•
18. •		•
17. •		•
15. ●		•
15. •		•
14. •		•
13. •		•
12. •		•
11. •		•
10.		•
9.		•
©°• °	00 00 0	• • • •
8. •		•
7. •		•
6.		•
5. ●		•
4.		•
3. •		•
2.		•
1. •		•
*	*	*

* = FIXED SHELF HOLES & KICK

Place metal runners in their correct hole positions (see above DIAGRAM 1) making sure CL = LEFT HAND GABLE & CR = RIGHT HAND GABLE, then attach using the special 7.5 euro screws provided. (see diagram to the right).

Executive Series					
Models			e Series red Shelf Position		
EXC – 4J	1 – 8 – 15 - 22	N/A			
EXC – 43					
	1 - 8 - 15 - 20 -				
EXC – 4B	8 – 16 – 24 - 32	N/A			
EXC – 2B	8 – 14	N/A			
EXB - 5C	1 – 8 – 15 – 20 –				
EXB – 4J	1 – 8 – 15 – 20	N/A	-		
EXB – 4B	8 – 16 – 22 – 28	N/A	\		
	Executive 750 'H' SERIES				
Models	Hole Positions	CAM PIN	I-Hole Positions		
HS		8			
H1	1	8			
H2	1 – 6	11			
H3	1 – 8 – 13	20			
MAXI ULTRA 'H' SERI		SERIES			
Models	Hole Positions	CAM PIN	I-Hole Positions		
H1	1	8			
HS2	1	8 –	- 15		
H2	1 – 8	13			
HS		8			
	MAXI ULTRA & ULTRA SERIES				
	WAXI OLINA G	ULIRAS	<u>eries</u>		
Models	Hole Positions	Models	Hole Positions		
Models 450					
	Hole Positions	Models	Hole Positions		
450	Hole Positions 1-6-11-16	Models LSD550	Hole Positions		
450 315C	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21	Models LSD550	Hole Positions 1-8 1		
450 315C	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21	Models LSD550 LSD330	Hole Positions 1-8 1		
450 315C 515	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21 MAXI	Models LSD550 LSD330	Hole Positions 1-8 1 SRIES Shelf Position		
450 315C 515 Models	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21 MAXI Hole Positions	Models LSD550 LSD330 & MSM SE Fixed	Hole Positions 1-8 1 SRIES Shelf Position		
450 315C 515 Models 16J3	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21 MAXI Hole Positions 1 - 8 - 15	Models LSD550 LSD330 C & MSM SE Fixed 22 25 36	Hole Positions 1-8 1 SRIES Shelf Position		
450 315C 515 Models 16J3 C16	Hole Positions 1-6-11-16 1-8-15-20 1-6-11-16-21 MAXI Hole Positions 1 - 8 - 15 1 - 8 - 15 - 20 -	Models LSD550 LSD330 C & MSM SE Fixed 22 25 36	Hole Positions 1-8 1 SRIES Shelf Position		





WARRANTY

Our goods come with guarantees that cannot be excluded under the Australian Consumer Law. You are entitled to a replacement of refund for major failure.

10 Year Warranty

- If the purchaser has a fault or defect with this product, the purchaser needs to contact Multistore Industries (Aust) directly on (07) 3208 6799 and state date of purchase, place of purchase and proof of purchase.
- Multistore Industries (Aust) will replace any faulty or defect parts at no cost to the customer. A replacement will be sent to you as soon as possible, or product can be exchanged at the store of purchase.
- This warranty is in addition to other rights and remedies of the customer under law.

Sincerely,

Multistore Industries (Aust) Management