
2 PCS



SALICE 105° SOFT CLOSE HINGE

Full Overlay - Clip On Also fits Blum drill pattern









Mounting Instructions for doors with Blum drill pattern.


Door




Cup fixed with pre-mounted spreading dowels.

Cabinet





Join the two points marked by an arrow.



Apply light pressure.







HAFELE


Adjusting the Door

Depth adjustment of door with SALICE mounting plates.

With the SALICE mounting plates with quick fixing system, a depth adjustment of the door from -0.5 mm up to +2.8 mm is possible via eccentric. It is not necessary to loosen further screws.








Height adjustment of door with SALICE cruciform mounting plates with slot.

Height adjustment of door of ±2 mm is possible by loosening the two fixing screws. The slots allow the mounting plates to slide in both directions. Afterwards the screws must be re-tightened.



0.7






Lateral adjustment of door with SALICE concealed hinges.

The adjusting screw produces the lateral travel of the hinge arm from -1.5 mm up to +4.5 mm. This value is reduced to -0.5 mm when using profile door hinges and mini hinges. The door moves with respect to the furniture side without coming apart. There are no further correcting actions required.



















Mounting Instructions for doors with Blum drill pattern.

Tools Required:

> No 2 Pozidrive Screwdriver / Screw Bit





ARTICLE # 483.02.405

HÄFELE AUSTRALIA PTY. LTD 8 MONTEREY RD DANDENONG VIC 3175 730.83.638

