
2 PCS


# HAFELE

**SALICE** 105° SOFT CLOSE HINGE

Full Overlay - Clip On









## Drilling Instructions


#### Mounting Instructions


#### Hinge Cup (Door)







#### Mount Plate (Cabinet Side)





Join the two points marked by an arrow.





Apply light pressure.







## HAFELE


#### Adjusting the Door

### Depth adjustment of door with SALICE mounting plates.

With the SALICE mounting plates with quick fixing system, a depth adjustment of the door from -0.5 mm up to +2.8 mm is possible via eccentric. It is not necessary to loosen further screws.








### Height adjustment of door with SALICE cruciform mounting plates with slot.

Height adjustment of door of ±2 mm is possible by loosening the two fixing screws. The slots allow the mounting plates to slide in both directions. Afterwards the screws must be re-tightened.



0.7






## Lateral adjustment of door with SALICE concealed hinges.

The adjusting screw produces the lateral travel of the hinge arm from -1.5 mm up to +4.5 mm. This value is reduced to -0.5 mm when using profile door hinges and mini hinges. The door moves with respect to the furniture side without coming apart. There are no further correcting actions required.



















#### **Tools Required:**

- > 35mm Ø Drill Bit & Template Kit
- > 2mm Ø Drill Bit
- > Pencil
- > Power Drill
- > No 2 Pozidrive Screwdriver / Screw Bit

#### Screw fixing

Cup fixed with screws (countersunk head).



Salice Hinge Drilling Pattern



ARTICLE # 483.02.400

HÄFELE AUSTRALIA PTY. LTD 8 MONTEREY RD DANDENONG VIC 3175 730.83.632



